

ft line technical details

ft line 1	ft line 2	ft line Ve	ft line 3
<p>Ref: 795400 FT GAC activate carbon filter assembly kit Sink Tap. Suitable for domestic use and vending.</p> 	<p>Ref: 795401 Set of two FT filters. 5µ polypropylene and GAC. Suitable for domestic use and catering sector.</p> 	<p>Ref: 795403 Set of two FT filters. 5µ polypropylene and act. carbon with silicopoliph. Suitable for catering and vending sectors.</p> 	<p>Ref: 795402 Set of two filters (activate carbon and 5µ polypropylene) and ultrafiltration membrane. Suitable for domestic use.</p> 
<p>Equipment composition: 1 FT-88 silver carbon filter, 1 FT cap, 1 wall bracket, 1 sink tap model Oslo, 1 valve 3/8, 1 wall tap, 1 tube 3/8 set.</p>	<p>Equipment composition: 1 FT-82 filter 5µ, 1 FT-88 silver carbon filter, 2 FT caps, 1 wall bracket, 1 sink tap model Oslo, 1 valve 3/8, 1 wall tap, 1 tube 3/8 set.</p>	<p>Equipment composition: 1 FT-82 filter 5µ, 1 silver carbon FT filter and silicopoliphosphate FT-90, 2 quick 3/8 connections.</p>	<p>Equipment composition: 1 FT-82 filter 5µ, 1 FT-88 silver carbon filter, 1 FT-91 ultrafiltration filter, 3 FT caps, 1 wall bracket, 1 sink tap model Oslo, 1 valve 3/8, 1 wall tap, 1 tube 3/8 set.</p>
ft line basic			
	<p>FT-line 85 Ref: 795503 FT cationic resin filter for descalcification. Suitable for vending and catering sectors to protect hot water appliances. Equipment composition: 1 FT-85 cationic resin filter, 1 FT cap, 1 bracket, 2 quick 3/8 connections.</p>	<p>FT-line 88 Ref: 795504 FT GAC activate carbon filter with silver. It prevents the growth of the contamination in. Suitable for domestic use and catering sector. Equipment composition: 1 FT-88 silver GAC filter, 1 FT cap, 1 bracket, 2 quick 3/8 connections.</p>	<p>FT-line 90 Ref: 795506 FT GAC activate carbon filter with silver and silicoph. Suitable for use in hotels, vending and cool fountain sec. It removes the chlorine and protects against incrustations. Equipment composition: 1 FT-90 GAC-silicopoliphosphate filter, 1 FT cap, 1 bracket, 2 quick 3/8 connections.</p>
<p>FT-line 82 Ref: 795500 FT filter in 5µ polypropylene. Suitable for domestic use or prefilter in domestic osmosis. Equipment composition: 1 FT-82 filter 5µ, 1 FT cap 1 bracket, 2 quick 3/8 connections.</p>	<p>FT-line 87 Ref: 795502 FT filter for regulating pH and remineralising acid water. Suitable for regulating pH in acid water and reverse osmosis appliances. Equipment composition: 1 FT-87 remineralization filter, 1 FT cap, 1 holding bracket, 2 quick 3/8 connections.</p>	<p>FT-line 89 Ref: 795505 FT mixed bed resin filter for demineralisation. Suitable for laboratories when small quantities of highly-purified demineralised water is required. Equipment composition: 1 FT-89 mixed bed resin filter, 1 FT cap, 1 bracket, 2 quick 3/8 connections.</p>	<p>FT-line 91 Ref: 795507 FT ultrafiltration membrane. Suitable for use in the home, hotel and catering sector. Equipment composition: 1 FT-91 ultrafiltration membrane, 1 FT cap, 1 bracket, 2 quick 3/8 connections.</p>
<p>FT-line 83 Ref: 795501 FT filter with GAC activated carbon. Suitable for domestic use and catering sector. Equipment composition: 1 FT-83 filter, 1 FT cap, 1 bracket, 1 quick 3/8 connection.</p>			